

**MNX ABS 200/150 HT**



Sample photo

**Order symbol:** ABS 200/150 HT  
**Product nbr:** 6081929  
**Description:** Enclosure, ABS  
**Remarks:** Smoked transparent cover

**EAN:** 6418074014153  
**El. number:**  
 Finland: 3420655  
 Denmark: 8212023644  
 Italy: 7362130  
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
<b>mm:</b>	255	180	150	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>	10.0	7.1	5.9	Impact Resistance (EN 62262): IK 07

Materials:		Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
<b>Material:</b>	ABS	
<b>Base colour:</b>	RAL 7035	
<b>Cover colour:</b>	Smoked grey	
<b>Cover screws material:</b>	Polyamide	
<b>Cover screws colour:</b>	Black	
<b>Gasket material:</b>	TPE	

Temperatures:		Certificates:
<b>Short term:</b>	-40 ... 80 °C	Fimko
<b>Continuous:</b>	-40 ... 60 °C	Europe EN 62208: 2003
<b>Short term:</b>	-40 ... 175 °F	Gost R
<b>Continuous:</b>	-40 ... 140 °F	

Accessories:	
MIV 200	Mounting plate (Galvanized steel)
MIN 15	DIN-15 Mounting rail
MIN 20	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
MIV 20	DIN-35 Mounting rail
FP A 200/180	Front plate (Aluminium)
HFP 180	Front plate hinge series (2 pcs)
FP 22046	Wall fastening lug (4 pcs)

