17 SERIES (Type 173) MOULDED CASE CURRENT TRANSFORMERS



DESCRIPTION

A range of compact low cost moulded case current transformers suitable for primary currents from 40A to 750A with built in sealable terminal covers.

APPLICATION

For transforming various primary currents into 5A or 1A standard secondary using up to 30x15mm or 20x20mm busbars or cables up to 24mm diameter.







FEATURES

- Built in sealable terminal covers.
- Mounting feet supplied.
- Narrow width 70mm.
- Wide range of primary current


TECHNICAL SPECIFICATION

- Conforms to IEC185, BS 7626, BSEN 60044-1, IEC 60044-1 and IEC 61869-2.
- Rated system voltage 0.72/3kV.
- Ambient temperature range -5°C to +50°C.
- Continuous current 1.2 x rated current.

RANGE									5A Secondry			
	Class 1				Class 0.5				Class 0.5S			
VA	2.5	5	10	15	2.5	5	10	15	2.5	5	10	15
40/5	A1	_	-	-	-	_	_	-	-	-	-	_
50/5	В1	-	-	-	_	-	-	-	_	-	-	_
60/5	C1	_	-	-	_	_	_	-	_	_	-	_
80/5	D1	_	-	_	_	_	_	_	D9	_	-	_
100/5	E1	_	-	-	E5	_	_	-	E9	_	_	_
150/5	F1	F2	-	-	F5	F6	_	_	F9	F10	-	_
200/5	G1	G2	G3	-	G5	G6	-	-	G9	G10	-	-
300/5	Н1	H2	НЗ	Н4	Н5	Н6	Н7	_	Н9	H10	-	_
400/5	J1	J2	J3	J4	J5	J6	J7	-	K9	K10	-	_
600/5	K1	K2	КЗ	K4	K5	K6	K7	_	K9	K10	K11	_
750/5	L1	L2	L3	L4	L5	L6	L7	_	L9	L10	L11	_

1A secondary available by request. Class 0.2, 0.2S available by request.

Order Example: A 17 series Type 173 moulded case current transformer with 5A secondary and 600A primary 5VA class 0.5 is part number 175-5-K6



Our policy is one of continuous development and therefore specifications may change without notice.

HOWARD BUTLER LTD

CROWN WORKS, LINCOLN ROAD WALSALL WS1 2EB ENGLAND