

NEW Festoon Lights

AC LED Cable Lights 22 Metres, 110V, 16A

The Festoon LED work lights are ideal AC work lights for Industrial, construction applications. The 110V LED Festoon lighting is energy efficient, saving up to 80% electrical power making them a cost effective lighting solution for indoor and outdoor use.



X10 LED Lamps

22 Metre 2.0mm yellow arctic grade cable with 16A 110V CEE Plug

KEY FEATURES:

- 660 lumens per lamp
- Super bright LED lamps - 10 x 660 lumens per kit
- 22 Metre 2.0mm yellow arctic grade cable
- Lamp holders spaced every 2 metres
- Multiple festoons can be linked to form a longer light chain via a junction box
- IP65 Rating
- Low heat output - Saves 80% electrical power
- Long life LED lamps rated life of 30,000 hours
- Fitted with 16A 110V CEE Plug



PRODUCT CODE: NSFESTOON22M8W



Optional accessories:

14 Metre extension lead available (110v Only): SPCABLE14M

