

56234

One Piece Shovel, D Grip,  
379 x 345 x 90 mm, 1035  
mm, Red



Lightweight and durable shovel. Its one piece construction eliminates areas where bacteria can be harboured. Smooth surface makes it extremely easy to clean, ideal for use in food production areas for moving food ingredients or large quantities of food waste.

# Technical Data

Item Number	56234
Shovel Blade Size, L x W x H	379 x 345 x 90 mm
Material	Polypropylene
Suitable for Food Contact (EU 1935/2004), <sup>1</sup>	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	75 Pcs.
Quantity Per Layer (Pallet)	0 Pcs.
Box Length	1190 mm
Box Width	265 mm
Box Height	365 mm
Length	1035 mm
Width	346 mm
Height	140 mm
Gross Weight	1,846 kg
Net Weight	1,645 kg
Cubik metre	0,0501 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Max. drying temperature	120 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Mark 7	Yes
GTIN-13 Number	5705020562341
GTIN-14 Number (Box quantity)	15705020562348
Commodity Code	39241000
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact