

4

3

2

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	REVISED PER ECR-25-251607	26JUL2025	MDP	DR


- 1

STAMP AMP 22-18* APPROX. AS SHOWN
WIRE RANGE IS 22-16 AWG
- 2

MATERIAL COPPER PER ASTM B152.
- 3

FINISH: NICKEL PLATE 0.00762[.000300]
MIN EXT THK PER SAE AMS QQ-N-290
- 4

BODY MATERIAL THK: 0.787±0.051[.031±.002]



2500	TAPE & REEL	132082-3
1000	LOOSE PIECE	132082-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 343°C[649°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		TE Connectivity		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -	NAME TERMINAL, RING TONGUE STRATO-THERM, HEAT RESISTANT, WIRE SIZE: 22-16 AWG		
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm* [509-3,260] SOLID OR STRANDED			APVD ROHDE DANIEL F 30AUG2016 PRODUCT SPEC - APPLICATION SPEC 114-2162 WEIGHT -		
FOR ORDER ENTRY	1-800-526-5142			MATERIAL 	FINISH 	SIZE A3 CAGE CODE 00779 DRAWING NO C=132082 RESTRICTED TO -		
CUSTOMER DRAWING						SCALE 4:1	SHEET 1 OF 1	REV A4