



R080

Waterproof cut-resistant impact gloves, with a nitrile-dipped palm for excellent dexterity



Impact

Abrasion Protection



Cut

Liquid Spray and Splash



Oil



Light Duty

Highly cut-resistant waterproof impact gloves, with a nitrile-dipped palm for excellent dexterity

- **Enhanced grip and dexterity:** RINGERS® R080 cut-resistant gloves feature a breathable knit shell with a nitrile-dipped palm, ensuring comfort and dexterity, while a sandy finish delivers excellent grip in wet and dry environments
 - **Added safety and comfort:** These RINGERS® gloves' waterproof liner keeps hands comfortably dry
 - **Specialized protection:** Developed with F3 Technology™ and a patented TPR (thermoplastic rubber) design covering knuckles, thumb and full length of the fingers, these work gloves minimize impact hazards* and offer highly advanced 360° cut resistance**
 - **Enhanced features:** RINGERS® R080 impact gloves also boast a high-visibility palm and finger design, for added safety, as well as touchscreen-compatible thumb tips, index and middle fingers
- *ANSI/ISEA 138-2019 Level 2 impact protection
**ANSI/ISEA 105-2024 CUT A6 and EN ISO F protection



Industries

- Oil and gas
- Industrial
- Construction
- Automotive
- DIY
- Mining

Applications

- Handling of tools
- Pipe handling
- Cleaning
- Handling of metal sheets



R080

Waterproof cut-resistant impact gloves, with a nitrile-dipped palm for excellent dexterity

Key Features

- **Knit shell with sandy finish:** Breathable comfort and superb grip
- **Waterproof barrier:** For dry, comfortable hand safety
- **Patented TPR design:** Knuckles, thumb and finger protection*
*ANSI/ISEA 138-2019 Level 2

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R080	Finishing: PVC Bumpers, Dipped Coating Material: Nitrile Liner Material: HPPE Cuff Style: Knitwrist		8, 9, 10, 11, 12	Hi Viz	8 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

