

Rittal – The System.

Faster – better – everywhere.

► PDU international, basic version – DK 7955.110

Date : Aug 27, 2014

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PDU international, basic version – DK 7955.110

created : 27.08.2014 build on www.rittal.com/uk-en



Product description

Description: Robust, compact basic power distributor for the IT environment. Thanks to the compact PDU, any IT rack may be easily equipped with a professional power distribution system. With the TS IT rack, assembly is even tool-free. The compact design allows simple assembly.

Material: Aluminium section, black anodised

**Protection category
IP to IEC 60 529:** IP 20

Packs of: 1 pc(s).

EAN: 4028177684911

**Customs tariff
number:** 85369085

Product features

Design: PDU Basic

Sockets: 24 / IEC 320 socket C13
4 / IEC 320 socket C19

To fit: Enclosure type: TS IT
TS 8
Height: 1200 mm

Infeeds: Qty.: 1
Phases per infeed: 1~


Length: 970 mm

Length of connection cable:	3 m
Ambient conditions:	Operating temperature: +0°C...+45°C
Type of electrical connection:	CEE
Rated current (max.):	16 A
Weight:	3.3 kg

Approvals

Declarations:  [Declaration of conformity \(DE\)](#)

Downloads

Data sheets:  [Technical details \(EN\)](#)

Documentation:  [Instructions \(EN, DE\)](#)
 [Instructions \(FR, EN, DE\)](#)