

# Rittal – The System.

Faster – better – everywhere.

## Glazed door for VX – VX 8618.050

Date : Jun 14, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Glazed door for VX – VX 8618.050

created: 14.06.2019 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Description:</b>	Instead of a sheet steel door or rear panel.
<b>Material:</b>	Frame: Extruded aluminium section Viewing window: Single-pane safety glass, 3 mm
<b>Surface finish:</b>	Powder-coated
<b>Colour:</b>	Frame: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
<b>Protection category IP to IEC 60 529:</b>	IP 55
<b>IK Code:</b>	IK08
<b>Supply includes:</b>	Glazed door Locking rod with double-bit insert 180° hinges (4)
<b>Note:</b>	Lock components for frame 8618.110 are required when mounting instead of the rear panel

## Product features

<b>To fit:</b>	Width: = 800 mm Height: = 2200 mm
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	18.8 kg

<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177921023
<b>Customs tariff number:</b>	94039010
<b>ETIM 6.0:</b>	EC000747
<b>ETIM 5.0:</b>	EC000747
<b>eCl@ss 8.0/8.1:</b>	27182204
<b>eCl@ss 7.0/7.1:</b>	27182290
<b>eCl@ss 6.0/6.1:</b>	27182290
<b>eCl@ss 5.1/5.1.4:</b>	27182201
<b>Product description:</b>	VX Glazed door, for WH: 800x2200 mm
<b>Approvals</b>	
<b>Approvals:</b>	UL + C-UL
<b>Certificates:</b>	IK-Code