

# MB10/10.L3



Products Low Voltage Products and Systems Connection Devices Terminal Blocks Solution Series

## General Information

<b>Extended Product Type:</b>	MB10/10.L3
<b>Product ID:</b>	1SNA115329R2400
<b>EAN:</b>	3472591153293
<b>Catalog Description:</b>	MB10/10.L3 Distribution Terminal Blocks
<b>Long Description:</b>	MB10/10.L3 Distribution Terminal Blocks - Grey,10mm <sup>2</sup> RatedCrossSection, 32.5mm Spacing G32, TH 35-7.5, TH 35-15 Rail.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Color:</b>	grey
<b>Connection Type:</b>	Screw clamp
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	85369010
<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-G Distribution terminals
<b>Declaration of Conformity - CE:</b>	1SND225007U1000
<b>EAC Certificate:</b>	1SND161009A1100
<b>EAN:</b>	3472591153293
<b>ETIM 4:</b>	EC001894 - Distributor assembly terminal blocks
<b>ETIM 5:</b>	EC001894 - Distributor assembly terminal blocks
<b>ETIM 6:</b>	EC001894 - Distributor assembly terminal blocks
<b>Environmental Information:</b>	1SND220038E1002
<b>Flammability According to UL94:</b>	V2
<b>Function:</b>	Distribution
<b>IT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-G Distribution terminals
<b>Invoice Description:</b>	MB10/10.L3 Distribution Terminal Blocks
<b>Minimum Order Quantity:</b>	5 piece
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Levels:</b>	1
<b>Object Classification Code:</b>	X
<b>Order Multiple:</b>	5 piece
<b>Package Level 1 EAN:</b>	3472591153293
<b>Package Level 1 Gross Weight:</b>	0.3 kg
<b>Package Level 1 Height:</b>	48 mm
<b>Package Level 1 Length:</b>	120 mm
<b>Package Level 1 Units:</b>	5 piece
<b>Package Level 1 Width:</b>	77 mm
<b>Package Level 2 Gross Weight:</b>	8.75 kg
<b>Package Level 2 Height:</b>	150 mm
<b>Package Level 2 Length:</b>	500 mm
<b>Package Level 2 Units:</b>	140 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 3 Units:</b>	6720 piece

Package Level 3 Units:	0/20 piece
Pollution Degree:	2
Product Main Type:	MB10/10
Product Name:	Terminal Block
Product Net Depth:	40.5 mm
Product Net Height:	44.5 mm
Product Net Weight:	60 g
Product Net Width:	32.5 mm
Product Packing Type:	Box
Rated Cross-Section:	10 mm <sup>2</sup>
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	8 kV
Recommended Screw Driver:	5.5 mm
RoHS Information:	1SND230023F0202
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	grey Distribution Terminal Blocks MB10/10.L3
Spacing:	10 mm
Sub-Function:	Phases
Tightening Torque:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m
Wire Stripping Length:	12 mm

