

Data sheet

Commercial Art.No.: 76.352.0736.0

hood MIN GOT GB 7 M20 25 Z0

Hood revos MINI made of zinc, straight with cable gland M20 (IP54), lowversion



Technical data

general

housing material	die-cast zinc
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	3
model of the housing	male
locking mechanism	single locking lever
cable entry	above
type of cable	gland nut
with cable screw gland	yes
thread size M	20
thread size PG	
hinged lid	no
EMC-version	no
length	26.8 mm
width	33.5 mm
height	57 mm

classification

ECLASS 11	
ECLASS 8.1	27440202
ETIM 9.0	EC000437

ETIM 8.0	EC000437
ETIM 7.0	EC000437
ETIM 6.0	EC000437
ETIM 5.0	EC000437
ETIM 4.0	EC000437
ETIM 3.0	EC000437

product compliance

ROHS conformity status	compliant
REACH-SVHC conformity status	compliant