

FEATURES

- S/FTP Shield
- Bare copper conductor
- Cat6a performs at longer lengths than a cat6
- RJ45 Connector assembled
- Various lengths available

RS PRO Cat6a Cable

RS Stock No.: 778-5133



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS Pro, Cat6a cable suitable for home, office and industrial networks requiring a reliable internet connection. These cables are LSZH (Low Smoke Zero Halogen) ensuring health and safety standards are met in the event of it being near a high heat source

General Specifications

Terminated/Unterminated	Terminated	
Connector Type	Male RJ45/ Male RJ45	
Shield Type	S/FTP	
Outer Sheath Material	LSZH	
Sheath Colour	Grey	
Conductor Material	Bare Copper	
Insulator Material	Polyolefin	
Tape Material	Aluminium / Polyester	
Tape Coverage	125	

Electrical Specifications

Frequency	250MHz	

Mechanical Specifications


Length	3m
Outer Diameter	6.0 +/- 0.20
Sheath Thickness	0.5mm
Insulator Diameter	0.97mm +/-0.05
American Wire Gauge	26



Approvals

Compliance/Certifications	2011/65/EU and 2015/863	
Standards Met	IEC 61935-2, ISO/IEC 11801 (2nd Edition): 2010, TIA 568C	





Construction	Value	
Conductors	AWG Size(mm) Material	26 7/0.20 +/- 0.008 Bare Copper
Insulators	Diameter (mm) Material	0.97+/-0.05 Polyolefin
Jacket	External O.D Thickness (mm) Material	6.0 +/- 0.20 0.5 PVC or LSZH
Таре	Material Coverage	Aluminium/Polyester 125