

Data sheet

Technical data

Mains connection	1~230 V, 50 Hz
Rated power P_2	370 W
Control	Without frequency converter
Activation type	Direct online (DOL)
Electromagnetic compatibility	EN 61000
Connection standard	EN 1254
Installation	Floor installation

Dimensions

Dimensions $H1$	775.0 mm
Dimensions $H2$	730.0 mm
Dimensions $H3$	225.0 mm
Dimensions $H4$	545.0 mm
Dimensions $H5$	590.0 mm
Dimensions L	455.0 mm