

DOUBLE EAR O CLIPS IN BAG

Stainless steel - INOX 304L double O clips



Part number	Ø min/max (mm)	Net weight (Kg)	Pack.
INOX 709P	7.00 / 9.00	0,015	1
INOX 911P	9.00 / 11.00	0,0205	1
INOX 1315P	13.00 / 15.00	0,032	1
INOX 1518P	15.00 / 18.00	0,04	1
INOX 1720P	17.00 / 20.00	0,0392	1
INOX 2023P	20.00 / 23.00	0,026	1
INOX 2327P	23.00 / 27.00	0,04	1