

Han CGM-PVDF M25x1,5 8,0-5,0



Image is for illustration purposes only. Please refer to product description.

Part number	19 15 503 5290
Specification	Han CGM-PVDF M25x1,5 8,0-5,0
HARTING eCatalogue	https://harting.com/19155035290

Identification

Category	Accessories
Series of hoods/housings	Han [®] F+B
Type of accessory	Cable gland

Technical characteristics

Wrench size	27 29
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68
Size	M25
Clamping range	5 ... 8 mm

Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	Black
Material (seal)	TPE
Colour (seal)	Blue
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
California Proposition 65 substances	Not contained

Commercial data

Packaging size	50
Net weight	0.023 kg
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140192782
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431