

FEATURES

- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight exposure
- **High Tensile Strength:** Supports up to 80 kg, ensuring secure bundling of heavy cables
- **Fire Behaviour UL 94 V-2:** Provides a level of flame retardancy, enhancing safety in fire-prone environments
- **Wide Operating Temperature Range:** Functions effectively up to 85 °C, suitable for various environments
- **Nylon Material:** Offers durability and flexibility, ensuring long-lasting performance

RS PRO Heavy Duty Cable Tie, 914 mm Nylon

RS Stock No: 656-066



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO heavy duty cable ties are designed for securing and organising large bundles of cables or wires. Made from durable nylon, they offer a reliable solution for managing cables in various industrial settings. With a maximum bundle diameter of 275 mm, they are ideal for heavy-duty applications where strength and durability are essential.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	80 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	914 mm
Material	Nylon
Maximum Bundle Diameter	275 mm
Width	9 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---