



## BS 100-PP10

Flat Type Fuse, 100A

### Product Properties:

Explosion-proof	No
Release characteristic	Medium time-lag
Optical defect indication	Yes
Type of current	DC
Colour code	Other
Nominal voltage DC	32 V
Max. continuous voltage DC	32 V
Number of fuses	10 .
Model	Other
Nominal current	100 A

### Dimensions:

Width	41 mm
MOQ	10 .
Unit	pck
Mounting holes	M5
Centre-to-centre distance of connections	30 mm
Length	11 mm

### Approvals:

### Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (250 Subs. 25 June 2025)
RoHS	RoHS 3 (2015/863)

SCIP

Not Applicable

### **Other information:**

<b>ETIM-Class</b>	EC004122 - Strip fuse
<b>ETIM-Release</b>	DYNAMIC
<b>Trademark</b>	NECORE
<b>Product Group</b>	Bolt-on / Strip fuses - Pin-pac
<b>Search Description</b>	BLADSÄKRING, 100A
<b>Alternative SKU</b>	BS100-PP10

### **Logistic information:**

<b>Barcode</b>	733117610375
<b>Country of origin</b>	TR
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	10 .
<b>Stock code</b>	BS 100-PP10
<b>Taric code</b>	85361090
<b>Unit</b>	pck

\*We reserve the right to make technical changes and disclaim any typographical errors.