

Rittal – The System.

Faster – better – everywhere.

► TopTherm wall-mounted cooling unit Total cooling output 0.30 kW – SK 3302.200

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TopTherm wall-mounted cooling unit Total cooling output 0.30 kW – SK 3302.200

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Description: Compact wall-mounted cooling units, with nano-coated condenser.

Material: Stainless steel 1.4301 (AISI 304)

Colour: RAL 9007

Protection category IP to IEC 60 529: External circuit IP 34
Internal circuit IP 54

Supply includes: Nano-coated condenser
Fully wired ready for connection (plug-in terminal strip)
Drilling template
Assembly parts

Note on Model No.: Extended delivery times.

Product description

Variant: wall-mounted

Total cooling output to DIN EN 14511: L 35 L 35 at 50 Hz: 0.32 kW
L 35 L 35 at 60 Hz: 0.34 kW
L 35 L 50 at 50 Hz: 0.19 kW
L 35 L 50 at 60 Hz: 0.21 kW

Air throughput (unimpeded air flow): External circuit: 310 m³/h
Internal circuit: 345 m³/h

Rated operating voltage:	230 V, 1~, 50 Hz/60 Hz
Dimensions:	Width: 280 mm Height: 550 mm Depth: 140 mm
Temperature control:	Basic controller (factory setting +35 °C)
Temperature range:	Bearing: -40 °C...+70 °C Operation (environment): +10 °C...+55 °C Setting range: +30 °C...+55 °C
Refrigerant/cooling medium:	Refrigerant: R134a Quantity: 0.1 kg Global Warming Potential (GWP): 1430 CO ₂ equivalent (CO _{2e}): 0.14 t
Power consumption P_{ei}:	L 35 L 35 at 50 Hz: 0.29 kW L 35 L 35 at 60 Hz: 0.31 kW L 35 L 50 at 50 Hz: 0.3 kW L 35 L 50 at 60 Hz: 0.33 kW
Rated current max.:	At 50 Hz: 1.6 A At 60 Hz: 1.7 A
Start-up current max.:	At 50 Hz: 3 A At 60 Hz: 3.4 A
Miniature circuit-breaker/fuse:	10 A
Permissible operating pressure (p. max.):	25 bar
eCl@ss 8.0/8.1:	27180704
Energy efficiency ratio (EER) 50/60 Hz L35 L35:	1,1 / 1,1
Packs of:	1 pc(s).
Weight/pack:	13 kg
EAN:	4028177379602
Customs tariff number:	84158200
ETIM 7.0:	EC000855
ETIM 6.0:	EC000855
eCl@ss 8.0/8.1:	27180704

eCl@ss 6.0/6.1:	27180704
Product description:	SK cooling unit TopTherm, wall-mounted, 0.36 kW, 230 V, 1~, 50/60 Hz, Stainless steel, WHD: 280 x 550 x 140 mm
Approvals	
Approvals:	Approval overview CCC exception letter CSA UL + C-UL - FTTA UR + C-UR
Certificates:	EAC
Declarations:	Declaration of conformity Declaration of conformity - F-gas regulation