

Micro Coaxial Cable

There's More Than Meets the Eye



AlphaWire

Cables you trust. Service you deserve.



Alpha's micro coaxial cable is a great space-saving solution that makes routing easier in applications such as medical probes, endoscopy systems, oximetry systems, industrial inspection, and more.

Alpha Wire's micro coaxial cable is perfect for a wide range of applications where space is at a premium, from sensitive medical imaging to industrial inspection. Our broad offering includes a full range of standard sizes from 50 to 32 AWG using high-strength silver-plated or tinned-copper alloys and rated to +200°C. The PFA dielectric and jacket provide stable properties for outstanding signal integrity, low capacitance, and consistent controlled impedance.

All items are in stock and ready to sample or ship for immediate delivery.

- 50 Ω characteristic impedance
- Exceedingly small and light weight
- 50 AWG to 32 AWG conductor range
- Stranded conductors for increased flexibility
- 30 V_{rms} voltage rating
- 90% shield coverage for excellent EMI protection and electrical characteristics
- Up to +200°C temperature range

Alpha Wire

US/International: 1-800-52 ALPHA | Europe: 01 932 772 422 | Asia Pacific: +86-21-61498201/61498205
www.alphawire.com | info@alphawire.com

Specifications

Operating Temperature

- 70°C to +200°C (Silver-plated copper alloy)
- 70°C to +150°C (Tinned copper alloy)

Characteristic Impedance

- 50 Ω

Voltage Rating

- 30 V_{rms}

Bend Radius

- 10x cable diameter

Materials

- Silver-plated or tinned copper alloy center conductor
- PFA dielectric
- White PFA jacket

Shielding

- Silver-plated or tinned copper alloy braid or spiral shield, 90% coverage minimum

Availability

- 100 m (328 ft) spools

Custom Configurations

- Composites
- Bundles



Part No.	Wire Size (AWG)		Stranding		Jacket Diameter		DCR, Max. (Ω/1000 ft @ 20°C)	Ground Cap, Nom. (@ 1 kHz)		Attenuation, Max. (@ 10 MHz)	
	AWG	mm ²	AWG	mm	Inch	mm		pF/Ft	pF/m	(dB/100 Ft)	(dB/m)
Silver-Plated Copper Conductors Silver-Plated Copper Braid Shield, 90% Coverage								-70°C to +200°C VP: 69% Impedance: 50 Ω ± 2 Ω UL AWM 1745			
9432	32	0.034	7/40	7/.079	0.044	1.12	168.6	29.9	98.1	4.1	0.13
9434	34	0.022	7/42	7/.064	0.039	0.99	271.9	29.9	110.2	5.5	0.18
Tinned Copper Alloy Conductor Tinned Copper Spiral Shield, 90% Coverage								-70°C to +150°C VP: 70% Impedance: 50 Ω ± 5 Ω			
9436	36	0.014	7/44	7/.051	0.021	0.53	478.2	33.6	110.2	7.6	0.25
9438	38	0.0088	7/46	7/.040	0.018	0.46	1005.8	33.6	110.2	11.6	0.38
9440	40	0.0055	7/48	7/.031	0.014	0.36	1424	33.6	110.2	13.7	0.45
Silver Copper Alloy Conductor Tinned Copper Spiral Shield, 90% Coverage								-70°C to +150°C VP: 70% Impedance: 50 Ω ± 5 Ω			
9442	42	0.0035	7/50	7/.025	0.012	0.30	2286	33.6	110.2	21.3	0.70
9444	44	0.0022	7/52	7/.020	0.010	0.25	3352.8	33.6	110.2	30.5	1.00
Silver Copper Alloy Conductor Silver Copper Alloy Spiral Shield, 90% Coverage								-70°C to +200°C VP: 70% Impedance: 50 Ω ± 5 Ω			
9446	46	0.0014	7/54	7/.016	0.008	0.20	4724.4	35.1	115.2	42.7	1.40
9448	48	0.0008	7/56	7/.012	0.007	0.18	7010.4	36.6	120.1	61	2.00
9450	50	0.0005	7/58	7/.010	0.006	0.15	11430	38.1	125.0	85.3	2.80

We can offer our micro coax cables in composite and bundled configurations using our Coast Custom capabilities. Create probe, catheter, and ultrasound cable for your custom medical or industrial application. Our custom hybrid bundled cables can combine multiple size coax cables along with other types of conductors or even lumens to carry gas or liquid!



GLOBAL HEADQUARTERS
711 Lidgerwood Avenue
Elizabeth, NJ 07207-0711 USA
Toll Free: 1-800-52 ALPHA
Tel: 1-908-925-8000
Fax: 1-908-925-5411
E-mail: info@alphawire.com

EUROPE
Alpha Wire International
Saxon House
1 Downside | Sunbury-on-Thames
Middlesex | United Kingdom | TW16 6RT
Tel: +44 1 932 772 422
Fax: +44 1 932 772 433
E-mail: europe@alphawire.com

ASIA PACIFIC
Alpha Wire
Silver Center | Room 1712
North Shanxi Road 1388
Shanghai | China | 200060
Tel: +86-21-61498201/61498205
Fax: +86-21-61498001
E-mail: apac@alphawire.com



AlphaWire

Cables you trust. Service you deserve.