
## fine filter LFMB-D-MINI-A

Part number: 192572 Classic

Without threaded connection plates with FRB threaded pin. 1  $\mu m$  filter cartridge, with metal bowl guard.

Modern alternatives can be found by entering the first four characters of the type code in the search field.





**FESTO** 

## **Data sheet**

Feature	Value
Series	D
Size	Mini
Design structure	Fibre filter
Grade of filtration	1 μm
Condensate drain	fully automatic
Operating pressure	2 12 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4]
	Inert gases
Air purity class at output	Compressed air to ISO 8573-1:2010 [5:7:3]
	Inert gases
Filter efficiency	99.99 %
Max. condensate volume	22 cm3
Bowl guard	Metal bowl guard
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	1.5 60 °C
Ambient temperature	-10 60 °C
Storage temperature	-10 60 °C
Residual oil content	0.5 mg/m3
Mounting type	Optional
	Line installation
	with accessories
Assembly position	Vertical +/- 5°
Pneumatic connection, port 1	Sub-base
Pneumatic connection, port 2	Sub-base
Material housing	Zinc die-casting
Material filter	Boron silicate fibre
Material bowl	PC
Materials note	Free of copper and PTFE
	Conforms to RoHS