




Chemical protection

VITAL 180

Dexterity and optimized resistance to oils and greases



CHEMICAL PROTECTION
TYPE B



SPECIFIC ADVANTAGES



Comfort

- Added comfort and absorption of perspiration, due to the cotton flock-lining



Guaranteed quality

- Chlorinated finish for better protection of products being handled
- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

INDUSTRIES

- Mechanical industry
- Other industries

APPLICATIONS

- Assembly of small oily parts
- Cleaning and general maintenance in wet environments



Chemical protection

VITAL 180

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
1 1 1 0 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
	K: Sodium hydroxide 40%
	P: Hydrogen peroxide 30%
	T: Formaldehyde 37%
TYPE B	
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Flocked
Exterior finish	Embossed texture, chlorinated
Material	Natural latex blended nitrile
Cuff characteristic	Straight cuff
Colour.s	Red
Length (cm)	30
Thickness (mm)	0.4
European sizes	6 7 8 9 10

LOGISTIC DETAILS

Packaging	1 pair/bag 10 pairs/box 100 pairs/carton
-----------	--

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/08/18/1638
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France