



9007AA1

LIMIT SWITCH LEVER ARM C +OPTIONS



Download your 9007AA1 datasheet



Characteristics | Documents & Downloads

Main Hide

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007A 9007B 9007C 9007N 9007T10 9007T5
Associated complete product	9007AW 9007C
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 0.88 in - offset: - -
Type of roller	1 steel outside roller diameter: 0.63 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

Complementary Hide

Switch actuation	By 30° cam
Product weight	0.1 lb(US)

Environment Hide

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

Offer Sustainability Hide

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be Compliant on 3Q2014 Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available download Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty Hide

Period

18 months