

# PT-E550WSP

## Handheld Electrician Labelling Printer



### Top Features:

#### Backlit graphic display

- Easy-to-read text and the ability to preview your label before printing.

#### Multiple power options

- Supplied with an AC adaptor and a rechargeable Li-ion rechargeable battery. Also works with 6 AA batteries (not supplied)

#### Lots of built-in contents

- Customise labels using a choice of 9 fonts, 7 frames and 384 symbols

#### Built-in auto full & half cutter

- Guaranteed to cut strong adhesive tapes
- Perfect for printing multiple/sequentially numbered labels
- With cut/pause to help reduce waste

#### Wi-Fi enabled

- Print to the device via the network
- Transfer content such as label templates, databases or custom symbols wirelessly from your PC to the PT-E550W
- Establish a P2P connection with your mobile devices (iOS and Android) in the direct mode to create label layouts on your Smartphone

#### Standard PC style keyboard

- Makes typing efficient.

#### Convenient labelling

- Handheld design and battery power lets you print labels wherever they are required.

#### Smart label application keys to save time

- General/Faceplate
- Cable Wrap/Cable Flag/Heat Shrink Tube/<sup>1</sup>Self-laminated
- Patch Panel / Punch Down Block
- Serialize / Advanced Serialize

#### Specialist HSe heat shrink tubes available

- HSe-211 (5.8mm)
- HSe-221 (8.8mm)
- HSe-231 (11.7mm)
- HSe-241 (17.7mm)
- HSE-251 (23.6mm)

### General

<b>Carton contents</b>	PT-E550WSP labelling machine 12mm black on white flexible ID tape cassette (8m) 18mm black on white laminated tape cassette (8m) 24mm black on white laminated tape cassette (8m) 24mm black on yellow laminated tape cassette (8m) Li-ion rechargeable battery AC adaptor Wrist strap Documentation USB-mini cable Software CD Carry case
<b>Language support</b>	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Brazilian Portuguese, Turkish

### Dimensions & Weights

<b>Without carton</b>	126(w) x 250(d) x 94(h)   1.05 kg
<b>With carton</b>	393(w) x 334(d) x 126(h)   3.25 kg
<b>Master carton</b>	413(w) x 348(d) x 390(h)   11.04 kg

### Built In Features

<b>Keyboard</b>	70 Key Rubber QWERTY/QWERTZ/AZERTY
<b>Dedicated number keypad</b>	Yes
<b>Interfaces</b>	USB, Wi-Fi
<b>Operating system support</b>	Microsoft Windows® Vista, Windows® 7, Windows® 8, Mac OS/X 10.7to 10.9.
<b>Display type</b>	Backlit Graphic Monochrome LCD with label preview capability
<b>Display resolution</b>	16 characters by 3 lines   128 x 64 dots
<b>Printing speed</b>	Up to 30mm/second
<b>Print resolution</b>	180dpi
<b>Maximum print height</b>	18.0mm
<b>Cutter type</b>	Auto Full & Half (with cut/pause feature) (fluorine-coated to cut strong adhesive tapes)
<b>Label length</b>	15mm minimum   999mm maximum
<b>Maximum lines per label</b>	7 (for 24mm wide tape)
<b>Tape margins</b>	Auto Cut: On/Off, Half Cut: On/Off, Chain Printing: On/Off, Special Tape: On/Off
<b>Vertical text printing</b>	Yes
<b>Mirror printing</b>	No
<b>Copies</b>	1 to 99
<b>Automatic numbering</b>	Yes (1 – 99, Normal, Simultaneous, Advanced)

### Label Creation

<b>Smart label application keys</b>	General, Faceplate, Cable Wrap, Cable Flag, Heat Shrink Tube, Patch Panel, Punch Down Block
<b>Fonts</b>	14   Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Calgary, Belgium, Atlanta, Adams, Brunei, Sofia, Germany, Letter Gothic
<b>Font styles</b>	9 (excl. Normal)   Normal, Bold, Outline, Shadow, Solid, Italic, Italic Bold, Italic Outline, Italic Shadow, Italic Solid
<b>Font sizes</b>	6, 9, 12, 18, 24, 36, 42, 48 point
<b>Symbols</b>	384
<b>Frames</b>	7
<b>Barcodes</b>	9   CODE39, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128 (UCC/EAN128), CODE128

### Memory

<b>Max. characters per label</b>	1,500
<b>Label memory locations</b>	99 (or up to 18,297 characters)
<b>Transferred content</b>	6 MB   Label templates: up to 99 Custom symbols: up to 99 Databases: up to 99

### Supplies

<b>Tape type</b>	TZe, HGe, HSe (Heat Shrink Tube)
<b>Tape widths</b>	3.5, 6, 9, 12, 18 & 24mm

### Optional Accessories

<b>Batteries</b>	BA-E001 Li-ion rechargeable battery AA alkaline/rechargeable batteries (LR6/HR6) x 6
<b>AC adaptor</b>	AD-E001