

## FEATURES

- Lockable protection window on all variants to enhance safety
- IP44 Rated, 0410185 is IP66 rated
- Wall mountable
- Red and blue colours offered in this range of power connectors
- Voltage ratings of 415V and 230V offered in this range
- Angled socket, allowing a more convenient connection
- All models offered in the range are highly reliable and excellent quality

## RS PRO IP44 Red Wall Mount 3P+N+E RCD Industrial Power Connector Socket, Rated At 32.0A, 415.0 V

RS Stock No.: 410-090



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description**

From the trusted brand RS PRO, comes a range of high-quality wall mountable power connectors. Manufactured to industry standards these connectors are easy to assemble and are a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

**General Specifications**

<b>Version</b>	With protection appliance
<b>Commercial Series</b>	DOMINO Series
<b>Pole Format</b>	3P+N+E
<b>Gender</b>	Female
<b>Body Orientation</b>	Angled
<b>Material</b>	Engineering Plastic
<b>Colour</b>	Red
<b>Applications</b>	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

**Electrical Specifications**

<b>Type of Current</b>	AC
<b>Current Rating</b>	32A
<b>Voltage Rating</b>	415V
<b>Working Frequency</b>	50Hz; 60Hz
<b>Plug/Socket</b>	Socket
<b>Termination Method</b>	Pre-Wired
<b>RCD Protection</b>	Main switch with RCD

**Mechanical Specifications**

<b>Mounting Type</b>	Wall Mount
----------------------	------------

## Protection Category

IP Rating

IP44

## Approvals

Compliance/Certifications

EN61340

