


## Datasheet

# Solid Wire Stripper Pliers

RS Stock number 540-1492



### Material

High carbon steel sheet (sk-5) for body of crimping tools, low carbon steel (s1018c) for lock screws and rivet

Medium carbon steel (ss41) for lock lid, PVC grip and spring steel for high tension return spring

### Finish

Grounding cut edges

Chemical black finish and red colour vinyl grip

### Hardness

Heat treated to HRC: 49 ~ 50.5 for body

HRC: 30 ~ 40 for Screws



ENGLISH

### **Contents**

1 pc-6-1/4" (155mm) serrated tip solid wire stripper pliers with lock lid, automatic return Spring and red colour vinyl grip - it fit to AWG 10~20 gauges wire, range for diameter of wire are 0.80 ~ 2.60 mm (thickness of blade - 3.2 mm and net weight - 125 grams).