

Datasheet

IEC Outlet-C13

RS Stock number 811-7193



Specifications:

Mounting Style:	Panel, Screw-type
Approvals:	UL(C,US), VDE, CE
Terminals:	Solder Type/Fast-on 4.8 x 0.80
Reference Standard:	IEC 60320-1
Permissible Temp with/without load:	0°C to +70°C
Permissible Temp for Soldering:	270°C for 5 sec. max.
Panel Thickness:	N/A
Material – Terminals:	Copper alloy, Tin plated
Material – Body:	Nylon – 6 GF 20%, V2
Insulation Resistance at 500 V DC:	1000MΩ min.
H.V. Break Down Test:	2KVAC for 1 minute
Contact Resistance (initial):	20m Ω max.
Current & Voltage Rating:	10A (VDE), 15A (UL, CSA) 250VAC

Unit: mm

