



Heat shrinkable tubing 2:1 - PVDF

TK20

Typical applications of this translucent tubing are where high-temperature performance is required. Also very suitable for applications that ask for visual inspection of covered components, or if a low friction surface is needed. TK20 is also used as oil stop for energy cables.

This thin walled, translucent heat shrink tubing is often used for chemical applications.

Features and benefits

- Semi-rigid heat shrinkable tubing made of PVDF
- Thin wall and tough
- For higher temperature applications
- Very good mechanical strength, abrasion resistance and chemical resistance
- Meets various industrial standards
- Self extinguishing, UL 224 VW1 listed



This thin walled, translucent heat shrink tubing is often used for chemical applications.

MATERIAL	Polyvinylidene Fluoride (PVDF)
Shrink Ratio	2:1
Operating Temperature	-55 °C to +175 °C
Min. Shrink Temperature	+175 °C
Longitudinal Change After Shrinkage	+/-10 % max
Dielectric Strength	≥ 30 kV/mm min. according to ASTM D2171
Flammability	UL 224 VW-1



Heat Shrinkable Tubing 2:1



TYPE	Supplied Ø D min.	Size (imperial)	Recov. Ø d max.	Wall (WT)	Length (L)	Colour	Designation as per VG-Norm	Tools	Article-No.
TK20-1.2/0.6	1.2	3/64 "	0.6	0.25	1.2 m	Transparent (CL)	VG 95343 T05 F 001 M	30-32	331-00129
TK20-1.6/0.8	1.6	1/16 "	0.8	0.25	1.2 m	Transparent (CL)	VG 95343 T05 F 002 M	30-32	311-00169
TK20-2.4/1.2	2.4	3/32 "	1.2	0.25	1.2 m	Transparent (CL)	VG 95343 T05 F 003 M	30-32	311-00249
TK20-3.2/1.6	3.2	1/8 "	1.6	0.25	1.2 m	Transparent (CL)	VG 95343 T05 F 004 M	30-32	311-00329
TK20-4.8/2.4	4.8	3/16 "	2.4	0.25	1.2 m	Transparent (CL)	VG 95343 T05 F 005 M	30-32	311-00489
TK20-6.4/3.2	6.4	1/4 "	3.2	0.30	1.2 m	Transparent (CL)	VG 95343 T05 F 006 M	30-32	311-00649
TK20-9.5/4.8	9.5	3/8 "	4.8	0.30	1.2 m	Transparent (CL)	VG 95343 T05 F 007 M	30-32	311-00959
TK20-12.7/6.4	12.7	1/2 "	6.4	0.30	1.2 m	Transparent (CL)	VG 95343 T05 F 008 M	30-32	311-01279
TK20-19.1/9.5	19.1	3/4 "	9.5	0.43	1.2 m	Transparent (CL)	VG 95343 T05 F 009 M	30-32	311-01909
TK20-25.4/12.7	25.4	1 "	12.7	0.48	1.2 m	Transparent (CL)	VG 95343 T05 F 010 M	30-32	311-02549
TK20-38.1/19.1	38.1	1-1/2 "	19.1	0.51	1.2 m	Transparent (CL)	-	30-32	311-03819
TK20-50.8/25.4	50.8	2 "	25.4	0.51	1.2 m	Transparent (CL)	-	30-32	311-05089

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.