

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0887283400**  
**Status:** **Active**  
**Overview:** Consumer USB Products  
**Description:** Universal Serial Bus (USB) Shielded I/O Cable Assembly: A-to-Pigtail Full-Rated, 2.08m Length

**Documents:**

[3D Model](#) [Packaging Specification PK-88728-002 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">88740</a>
Assembly Configuration	Single Ended Connector
Comments	Full-rated
Connector to Connector	USB Type A-to-Pigtail
Overview	<a href="#">Consumer USB Products</a>
Product Name	USB
UPC	800754341738

**Physical**

Cable Length	2.08m
Circuits (Loaded)	4
Gender	Male
Lock to Mating Part	Yes
Net Weight	69.600/g
Packaging Type	Bag
Pitch - Mating Interface	2.00mm, 2.50mm
Single Ended	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Round


**Electrical**

Current - Maximum per Contact	1.0A
Shielded	Yes

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-88728-002
Sales Drawing	SD-88738-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[88740 Series](#)

**Mates With**

Universal Serial Bus (USB) Type A Receptacle [67329](#) , [67230](#) , [89485](#)