

Illuminated selector switch actuator, RMQ-Titan, With thumb-grip, momentary, 2 positions, Blue, Metal bezel

**Part no. M30C-FWLK-B
187120**

Product name	Eaton Moeller® series M30 Illuminated selector switch actuator
Part no.	M30C-FWLK-B
EAN	4015081821693
Product Length/Depth	36 millimetre
Product height	47 millimetre
Product width	46 millimetre
Product weight	0.042 kilogram
Certifications	IEC/EN 60947 VDE 0660
Product Tradename	M30
Product Type	Illuminated selector switch actuator
Product Sub Type	None
Bezel color	Chrome
Bezel material	Metal
Design	With thumb-grip
Fitted with:	Front ring
Functions	Stay-put/spring-return function, can be changed with coding parts M22-XC-Y
Degree of protection	NEMA 4X, 13
Degree of protection (front side)	IP66
Lifespan, mechanical	100,000 Operations
Opening diameter	30 mm
Operating frequency	2000 Operations/h
Operating torque	0.3 N·m
Product category	RMQ-Titan
Size	Front dimensions: Ø 36 mm
Suitable for	Illumination
Switching angle	40 °
Type	Illuminated selector switch actuator
Mounting position	As required
Shock resistance	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	70 °C
Climatic proofing	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
Connection to SmartWire-DT	With SWD-RMQ connections Yes
Actuator color	Blue
Actuator function	Momentary Spring-return
Actuator type	Toggle
Number of switch positions	2

Force for positive opening - min		0 N
----------------------------------	--	-----

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Front element for selector switch (EC000222)			
Tecnología electrónica, de automatización y de mando de procesos / Tecnología de conmutación de baja tensión / Equipo de comando y señalización / Elemento frontal para conmutador-selector (ecl@ss10.0.1-27-37-12-13 [AKF031014])			
Number of switch positions			2
Type of control element			Toggle
Suitable for illumination			Yes
Colour control element			Blue
Colour indicator light cap			Blue
Construction type lens			Round
Hole diameter		mm	30
Width opening		mm	0
Height opening		mm	0
Switching function latching			No
Spring-return			Yes
With front ring			Yes
Material front ring			Metal
Colour front ring			Chrome
Degree of protection (IP), front side			IP66
Degree of protection (NEMA)			4X, 13