



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 8:21 (UTC)



6304DDU

Single-Row Deep Groove Ball Bearings



Parts Number

6304DDUC3

Boundary Dimensions

d	20	mm	Bore diameter
D	52	mm	Outside diameter
B	15	mm	Width
r (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	17500	N	Basic dynamic load rating
C0r	7900	N	Basic static load rating

Speeds

Grease	10000	min-1	Grease lubrication
--------	-------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	26.5	mm	Diameter of shaft abutment
da (max.)	28	mm	Diameter of shaft abutment
Da (max.)	45.5	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	12.4	Factor
----	------	--------

Additional information

z	7	Number of Balls	
Dw	9.525	mm	Ball Diameter

Mass

Mass approx.	0.145	kg	Mass approx.
--------------	-------	----	--------------

