

**2-65-005**

STANLEY® CUSHION GRIP™ Slotted Phillips Screwdriver Set (10 pc)

**STANLEY®**

**3253562650054**



**Product Description :**

Constructed with a large diameter soft grip handle, the STANLEY® CUSHION GRIP™ Screwdriver Phillips Slotted Set of 10 pc. is built for exceptional comfort, especially when carrying out repetitive professional work. Engineered from high-strength, chrome vanadium steel to reduce the chance of tip breakage, this high quality screwdriver is suitable for demanding high torque applications. The STANLEY® CUSHION GRIP™ Screwdriver Phillips Slotted Set of 10 pc. is designed to improve screw retention, and at the same time, enhance durability, reliability and product life. The handle is moulded directly to the bar for extra strength and a virtually unbreakable bond. And thanks to the clearly-marked tip ID on the handle, users can easily identify the correct screwdriver for each job.

**Product Features and Benefits :**

- CHROME VANADIUM STEEL BAR: Allows for high torque and reduces the chance of tip breakage
- COLOUR CODED ENDS: For easy identification of the correct screwdriver for each screw type
- HANDLE MOULDED DIRECTLY TO BAR: For a virtually unbreakable bond, delivering exceptional reliability and long product life
- LARGE DIAMETER HANDLE: Which offers great torque needed for driving wood screws
- ANTI-RUST: Nickel plated bar protects from rusting
- PRODUCT ID: On the handle allows for self selection at POS
- MAGNETIC TIPS: Easy pick up and screw locator
- SMOOTH DOMED END: Ensures fast spinning action with speed and comfort
- SOFT GRIP HANDLE: Perfect combination of great grip plus reduces fatigue

**Product Warranty :**

1 Year Warranty

**Product standards and norms :**

- Consult the Standards of each product within the Kit

