

Actuator

45-
2231.11G0.000

Distribution by
Rs-online



<https://rs-online.eao.com/component/45-2231.1...>

Your product:



45-2231.11G0.000 Actuator

FRONT

Front dimension:	Ø 29,5 mm
Front form:	Round
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Design:	Raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens colour:	Yellow
Lens material:	Plastic
Lens illumination:	Illuminated
Lens shape:	Flush
Lens optics:	transparent
Lens type:	Level with front bezel
Illumination colour:	Yellow

MECHANICAL CHARACTERISTICS

Switching action:	Momentary
Switching system:	Slow-make switching element

Mechanical lifetime: 3 Mil. cycles of operation
Operating frequency: Max. 3 600/h
Weight: 0.017 kg

AMBIENT CONDITION


IP front protection: IP66, IP67, IP69K
Operating temperature: – 25 °C ... + 70 °C
Storage temperature: – 40 °C ... + 80 °C
Shock resistance: According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms
Vibration resistance: According to IEC 60068-2-6: 20 ... 500 Hz: 5 g
Climate resistance: During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

CERTIFICATE

REACH: REACH compliant
RoHS: RoHS compliant

OTHER

Short Description: Actuator, Ø 22.3 mm, Ø 29,5 mm, Flush, Illuminated, Yellow, Plastic, transparent, Round, Black, Plastic, Momentary, IP66, IP67, IP69K, Yellow
Housing colour: Black
Housing material: Plastic
Wiring diagrams:



Mounting cut-outs:



Dimension drawings:

