

## Features

- PVC Hook-up Wire
- UL 1007 Equivalent
- Tinned Copper Conductors

## RS PRO Hook Up Wire

RS Stock No.: 0217313



*Representative Image - Colour will vary*

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Stranded flexible Hook-up Wire designed for the internal cabling of electrical and electronic equipment. Suitable for a broad range of applications from control cabinets to specialist machine tools

Hook-up wire is a flexible cable with a durable PVC protective sheath and tinned copper conductors, available in multiple colours, ideal for colour-coding cable installations.

The cable offers good insulation due to the PVC insulation material and installation is easy and efficient thanks to the flexible layout of the cable.

## General Specifications

|                                       |                     |
|---------------------------------------|---------------------|
| <b>Conductor</b>                      | Tinned Copper       |
| <b>Insulation</b>                     | PVC                 |
| <b>Insulation Colour</b>              | Blue                |
| <b>Approximate Diameter</b>           | 1.42 mm             |
| <b>Number of conductors</b>           | 1                   |
| <b>Conductor cross sectional area</b> | 24 AWG              |
| <b>Conductor construction</b>         | 7 strands of 0.20mm |
| <b>Length</b>                         | 305 MTRS            |

## Mechanical Specifications

|                            |        |
|----------------------------|--------|
| <b>Minimum temperature</b> | -20°C  |
| <b>Maximum temperature</b> | +105°C |

## Electrical Specifications

|                       |      |
|-----------------------|------|
| <b>Voltage rating</b> | 300V |
|-----------------------|------|