

ECOFLOW

EcoFlow DELTA Pro 3 Portable Power Station

4096Wh | 4000W Output



GENERAL

Colour

Silver

1 Unit Capacity Extend

12kWh

Dimension(L*W*H)

Approx. 693mm*341mm*410mm

Capacity

4096Wh

Max Extend Range

12kWh

Net.Weight(KG)

Approx. 51.5kg (113.54 lb)

AC OUTPUT

Max Continuous Output

4000W Max

Output Voltage

230V

X-Fusion

Yes, 230V/2900W AC input, 4000W.Max AC output

EPS/UPS

<10ms, UPS

AC Outlets

4x Type F, 230V/16A ; 1x CEE 16A, 230V/16A

Surge Output

8000W, 400ms

X-Boost

6000W, Max

X-Stream

Yes

AC Power IN/OUT Port (Discharge Only)

230V~17.4A 50Hz

DC OUTPUT

USB-C

USB-C*2, 5/9/12/15/20V 5A 100W Max

Car Power Output

No

Remote Control Port

1X

USB-A-Fast

USB-A*2, 5V 2.4A 9V 2A 12V 1.5A 18W Max

12V DC Output

12.6V/30A 378W Total ; DC5521, 1X, 5A Max ;
Anderson, 1X, 30A Max

INPUT

Utility Power Charging

C20 port, 220-240V 12.5A 50/60Hz 2900W Max
Bypass Mode: 220-240V 12.5A 50/60Hz

EV Charger Charging (AC Power IN/OUT Port)

AC Power IN/OUT Port
4000W Max, 220-240V 20A 50/60Hz

Car Input

12V 8A Max. 48V 20A Max.

0-80% Charge time

50min(1C Charging)

Adjustable AC Charging Speed

Yes

Solar Input

2600W, Max
2 Ports,
HPV:30-150V/15A, 1600W Max
LPV:11-60V/20A, 1000W Max

Generator Input

3200W, Max(with Smart generator 4000)

Bond Charge Input(with 1*EB)

7000W, Max

BATTERY

Extra Battery Port

2X, Support DP EB, DP3 EB

Life Cycle

>4000cyc, 80%

CTC Craftsmanship

yes

Battery Material

LFP

IP rate for Battery Pack

IP65