

FR08 - Bizflame Industry Two Tone FR Jacket

Collection: Bizflame™ Industry

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Industry: 80% Cotton, 19% Polyester, 1% Carbon Fibre, 340g

Outer Carton: 15

Product information

Designed for working in hazardous conditions both off-shore or on-site, this jacket combines style with performance. The special blend of FR Polyester in the fabric, provides unbeatable durability in the toughest of conditions.

Bizflame™ Industry

Bizflame™ Industry has been developed to perform in the toughest conditions. Ideal for industries such as oil and gas where durability is a must, Bizflame™ Industry is certified to a range of EN standards offering optimum protection in a range of hazardous situations. Styles in this range are metal free, minimising the risk of static electricity hazards and of damage to surfaces. Bizflame™ Industry FR polyester has been made from recycled fibres thereby reducing the production carbon footprint and working towards a sustainable future.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 11 CAL/CM², ATPV 13 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

EN 13034 Type 6

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV 16 CAL/CM² (HAF 83.7%))



Features

- Industrial laundry wash at 75°C and tunnel dry at 155°C
- Protection against radiant, convective and contact heat
- Hook and loop cuffs for a secure fit
- Adjustable waist for a perfect fit
- External standards label for quick identification of protection levels
- Certified protection against molten metal splash
- Non-magnetic - nickel and ferrous free
- 40+ UPF rated fabric to block 98% of UV rays
- Sew on flame resistant industrial wash tape
- Radio loops for easy clipping of a radio
- 5 pockets for ample storage

FR08 - Bizflame Industry Two Tone FR Jacket
Commodity Code: 6203321000

Test House

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
 Sebenhirtenstrasse 12A
 1230, Austria
 Contact: Marion Pfeiler
 Cert No: VN625 154930

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
 Sebenhirtenstrasse 12A
 1230, Austria
 Contact: Marion Pfeiler
 Cert No: 0598

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR08RBRS	Royal Blue	58.0	38.0	28.0	1.0400	0.0617	5036108309030	25036108797473
FR08RBRM	Royal Blue	58.0	38.0	28.0	1.0800	0.0617	5036108309023	25036108797466
FR08RBRL	Royal Blue	58.0	38.0	28.0	1.1000	0.0617	5036108309016	25036108797459
FR08RBRXL	Royal Blue	58.0	38.0	30.0	1.1700	0.0661	5036108309047	25036108797480
FR08RBRXXL	Royal Blue	58.0	38.0	30.0	1.2800	0.0661	5036108309054	25036108797497
FR08RBRXXXL	Royal Blue	58.0	38.0	30.0	1.3200	0.0661	5036108309061	25036108797503