

tesa 4959
Double-sided self-adhesive tape

**Product Description/
 Application:**

tesa 4959 is a double-sided mounting and splicing tape equipped with a non-woven backing and coated with an acrylic adhesive of very high tack and good shear strength, resistant to light and ageing, largely resistant to plasticisers.

It is suitable for:

- Mounting of signs, covers and name plates
- Mounting of plastic door linings in the car industry
- Self-adhesive mounting of plastic bags, dispatch bags, continuous stationery, posters, displays etc.
- Splicing of paper and film webs

Dimensions:

Stock Items	
Lengths	Widths
50 m 100 m	12, 19, 38 mm 6, 9, 12, 15, 19, 25,30, 38, 50, 60 mm

Also available in long rolls of up to 10.000 m and with fingerlift.
 Other dimensions on request.

Technical Data:
 (mean values)

Backing	Colour	Liner	Thickness ¹⁾	Adhesive	Adhesion on steel ¹⁾
non-woven fabric	transparent	silicone-coated paper	0,115 mm (without liner)	modified acrylic	15,5 N/25 mm

¹⁾ Parameters of the specification

tesa AG

P.O. Box 57 02 62
 D-22771 Hamburg
 Telephone +49-40-49 09 3360
 Telefax +49-40-49 09 4506

tesa self-adhesive tapes are used successfully in many sectors to solve a variety of problems. Our publications contain numerous examples of such uses, intended to help towards a solution of your particular problems. Each tesa product has been developed for a particular range of applications. Nevertheless, experience has shown that even for one and the same objective, the exact requirements may differ from case to case. We, therefore, recommend that you carry out your own tests in each case, to confirm that the tesa self-adhesive tape which you envisage using is appropriate for your particular application. The Advisory Section of our Technical Service Department will be happy to assist. All information and recommendations are given by us in good faith, on the basis of practical experience, but without warranty.