

## Han-Eco Outdoor 16A-HTE-M25



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 46 216 0446                                                                |
| Specification      | Han-Eco Outdoor 16A-HTE-M25                                                   |
| HARTING eCatalogue | <a href="https://harting.com/19462160446">https://harting.com/19462160446</a> |

### Identification

|                          |                  |
|--------------------------|------------------|
| Category                 | Hoods / Housings |
| Series of hoods/housings | Han-Eco® A       |
| Type of hood/housing     | Hood             |

### Version

|                         |                      |
|-------------------------|----------------------|
| Size                    | 16 A                 |
| Version                 | Top entry            |
| Number of cable entries | 1                    |
| Cable entry             | 1x M25               |
| Locking type            | Single locking lever |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Number of relockings                   | ≥500                                           |
| Degree of protection acc. to IEC 60529 | IP65                                           |

### Material properties

|                         |                                          |
|-------------------------|------------------------------------------|
| Material (hood/housing) | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)   | RAL 9005 (jet black)                     |
| Material (seal)         | FPM                                      |
| Colour (seal)           | RAL 7001 (silver-grey)                   |



**Pushing Performance**  
Since 1945

## Material properties

|                                           |                                                        |
|-------------------------------------------|--------------------------------------------------------|
| Material flammability class acc. to UL 94 | V-0                                                    |
| RoHS                                      | compliant with exemption                               |
| RoHS exemptions                           | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                                | compliant with exemption                               |
| China RoHS                                | 50                                                     |
| REACH Annex XVII substances               | Not contained                                          |
| REACH ANNEX XIV substances                | Not contained                                          |
| REACH SVHC substances                     | Yes                                                    |
| REACH SVHC substances                     | Lead                                                   |
| California Proposition 65 substances      | Yes                                                    |
| California Proposition 65 substances      | Lead<br>Nickel                                         |
| Fire protection on railway vehicles       | EN 45545-2 (2020-08) + A1 (2023-10)                    |
| Requirement set with Hazard Levels        | R22 (HL 1-2)<br>R23 (HL 1-3)                           |

## Specifications and approvals

|                |                                                             |
|----------------|-------------------------------------------------------------|
| Specifications | IEC 61984<br>EN 45545-2 Fire protection on railway vehicles |
| Approvals      | CE                                                          |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 69.2 g                                   |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140176294                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |