

Steel Scribers

- with tungsten carbide tips



ART N°	mm	shaft-ø mm	version
334606	175	14	straight bar, with red plastic handle
334608	150	6	hexagonal bar, galvanized, with clip
334609	180	8	hexagonal bar, galvanized, without clip
334610	150	8	hexagonal, aluminium shaft, lacquered, with drop mechanic
334695	35	—	spare tip, carbide, for 334610
334611	150	10	„RICO“-Marker, aluminium shaft, knurled handle, pen type
334694	70	—	spare tip, carbide, for 334611
334612	230	4	straight and cranked bar, exchangeable tips, knurled handle
334615	150	9	carbide marker, push technic, with clip
334690	30	—	spare tip, carbide, straight version, for 334615
334696	90	—	spare tip, carbide, straight version, for 334612
334697	100	—	spare tip, carbide, cranked version, for 334612

Steel Scribers

- with tungsten carbide needle
- with clip and magnet

- made of steel, black burnished
- with exchangeable needle
- with anti-slip knurled handle



with magnet



ART N°	mm	shaft-ø mm	version
334620	155	7.5	with tungsten carbide tip, anti-slip knurled handle
334629	—	3	spare part, tungsten carbide needle

Parallel Surface Gauge

- for simple workshop purposes

- round, chromed column, without graduation
- hardened steel scriber, straight and cranked bar
- scriber is rotatable and turnable
- round and lacquered iron base



ART N°	mm
342102	300
342104	500