

Kraus & Naimer 'C' Switches – Electrical & Mechanical Life

Switch Type	Mechanical Life (On-Off Operations - Million) For switching angle:				Electrical Life @ 380-440v & Max. Rating (On-Off Operations)	
	30°	45°	60°	90°	Util. Category AC-21A	Util. Category AC-3
CA4/CG4	1.0	1.3	1.5	1.3	100,000	150,000
CA10/CH10	1.5	1.8	2.0	1.5	100,000	150,000
CA20/CH16	1.5	1.8	2.0	1.5	100,000	150,000
CA25	1.5	1.8	2.0	1.5	100,000	150,000
C26	1.0	1.5	2.0	1.5	100,000	150,000
C32	1.0	1.5	2.0	1.5	100,000	160,000
C42	1.0	1.5	2.0	1.5	100,000	160,000
C43	0.4	0.45	0.5	0.45	100,000	160,000
C80	0.4	0.45	0.5	0.45	75,000	100,000
C125	0.4	0.45	0.5	0.45	75,000	100,000
C315	0.3	0.4	0.5	0.4	50,000	80,000