

D 19 L 19

Socket 1/2"

Bi-hexagon UD profile, long pattern

Code 6140410 ETIM EC002203
 EAN 4010886614044 UNSPSC 27-11-17-04
 Country of origin Germany eCl@ss 21-04-02-19
 Customs tariff number 82042000



Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- chrome vanadium steel, ground, chrome-plated
- Sizes 16, 18, 21 mm with hole drilled for tommy bar Ø 8 mm

Article information

Contents (Qty of pieces)	1	Standard	DIN 3124 DIN 3120 - C 12,5 ISO 1174
Net weight [kg]	0,175 kg	Width across flats 1 [mm]	19
Total length [mm]	82 mm	Backup	Ball Catching Cricket
Total width [mm]	26,7 mm	Insert-Ø 1	26,7 mm
Surface	polished, chrome-plated	Working length	82,0 mm
Material	Chrome-vanadium steel	Insert-Ø 2	26,0 mm
Drive connector square female (metric)	12,5 mm	Operating depth	22,0 mm
Drive connector square female [inch]	1/2"		