

# Cleaner XGT®

## CL003G

40Vmax • 200 mbar • 0,25 L

**XGT® powered high-suction vacuum cleaner with 4-mode power selection and a mode memory function.**

CL003G has two one-touch push button switches (one for ON/4-speed change, the other for OFF). Number of green lamp indicates the selected mode. Equipped with paper disposable dust bag as well as cloth dust bag.



### Technical specifications

|                                            |                          |
|--------------------------------------------|--------------------------|
| Voltage XGT                                | ✓                        |
| Nominal Battery Voltage                    | 40 V                     |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-ion) | Li-ion                   |
| Air volume                                 | 1,0 m³/min               |
| Max. sealed suction                        | 200 mbar                 |
| Suction power                              | 15 / 35 / 60 / 100 W     |
| Continuous use XGT® 40Vmax / 2.5 Ah        | 80 / 40 / 25 / 16 min    |
| Tank Capacity for Dust                     | 0,25 L                   |
| Sound Pressure Level (L <sub>pA</sub> )    | 54 / 59 / 62 / 65 dB (A) |
| Product net weight                         | 1,2 kg                   |
| Tool weight with battery                   | 1,9 - 2,5 kg             |
| Product Dimensions (L x W x H):            | 1121 x 113 x 177 mm      |
| Vibration Level (3 axes)                   | 0,1 m/s²                 |
| Brushless Motor                            | ✓                        |

### User benefits

- 4 modes with memory function
- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- Built-in LED light illuminates the work area
- Cleaning of tight places can be done without nozzle
- Ergonomic soft grip handle provides increased comfort
- Battery protection system automatically shuts off power when the battery level is low

Link to product - [www.makita.uk.com](http://www.makita.uk.com)



# Related products

## Optional AC

**123539-7**

Floor T-Nozzle 225 mm, Black



**127828-2**

Nozzle Assembly



**140H94-2**

Soft Brush 360 Complete Set, Blue



**1910D5-0**

Cyclone Pre-separator



**1910Y3-1**

TELESCOPIC PIPE SET



**191D73-9**

Cyclone Pre-Separator 400 ml



**191D77-1**

Straight Pipe



**191E30-3**

Flexible Hose Set



**191G86-8**

Nozzle assembly set



**199038-1**

Seat Nozzle Set 175 mm



**413809-5**

Sash Nozzle



**458942-6**

Suction Tube With Pipe Lock



**459038-6**

Nozzle Holder Black



## Other

User manual

Parts drawing