

TPSL01

Outdoor Single Gang Switch

Features & Benefits

- Single gang
- 2 way switching
- 2 x earth terminals in back box
- IP55 weatherproof rating
- Impact resistant housing
- 5 × 20mm cable entries (bottom entry supplied with cut to size grommet)



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface
Earth Class Rating	Class I
Operating Temperature	-10°C to 40°C
Ingress Protection Rating	IP55
Switch type	Single Pole - Single Gang 2 Way
Mounting Hole Centres (mm)	55
Switch rating	10A (2.3kW) 10AX
Cable Entry(s)	Multiple M20 Knockouts, x1 Grommet Bottom Entry

General

Data sheet

TPSL01

Safety / Powerseal Outdoor Power

Weight (g)	125.6
Height (mm)	85
Width (mm)	75
Depth (mm)	61
Body Construction	Polycarbonate
Product Colour	Grey
EAN Number	5012483009161
Guarantee Period	3 Years

Line Diagrams

