


C-160303

NUMBER

FITS TAB 0.8 (0.02) THICK.

CHAMFER



DIMENSIONS IN M.M. DO NOT SCALE PRINT DIMENSIONS THUS IN INCHES

6-160303.5	△ 3	PHOSPH. BRONZE	NONE
6-160303.4	△ 3	BRASS	TIN
6-160303.3		PH. BRONZE	△ 2
6-160303.2		PHOSPH. BRONZE	TIN-LEAD
6-160303.1		BRASS	TIN-LEAD
6-160303.0		PHOSPH. BRONZE	PRE-TIN
5-160303.9		BRASS	PRE-TIN
5-160303.8	△ 1	BRASS	TIN
5-160303.7	△ 1	BRASS	NONE
5-160303.6		PHOSPH. BRONZE	TIN
5-160303.5		PHOSPH. BRONZE	NONE
5-160303.4		BRASS	GOLD
5-160303.3		BRASS	SILVER
5-160303.2		BRASS	TIN
5-160303.1		BRASS	NONE

NOTE: △ 1 SPIRICE FREE, FOR AMP. D. MOTOR.
 △ 2 BRIGHT PRE-TINPLATED.
 △ 3 REELED WITH PAPER LAYER.

CUSTOMER COPY FOR REFERENCE ONLY

©1978 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



AMP-HOLLAND N.V.
 's-Hertogenbosch

WIRE RANGE 1.3-2.50 mm (22-20 AWG)	INSUL. RANGE 1.3-2.0 mm (0.050-0.080)	FIRST USED
--	---	------------

ORDER NO.	MATERIAL	PLATING
DR <i>[Signature]</i>	DATE 6.3.1978	DE DATE
CHK	DATE	APP <i>[Signature]</i> DATE 7.3.78

SCALE 4:1	SIZE A	NO	C-160303	REV 9
NAME .110 SERIES FASTON RECEPTACLE				