

FEATURES

- Flexible, lightweight and durable
- Mirror smooth inner for improved flow
- Resistant to a wide range of chemicals
- High resistance to moisture absorption
- Excellent abrasion resistance

RS PRO Air Hose Natural Nylon 10mm x 30m NLF Series

RS Stock No.: 415-0418



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Brought to you by RS Pro, a range of air hoses, ideal for the transfer or air, gas or fluid. Both Type 11 and Type 12 versions are available, providing solutions for areas requiring low toxic and food safe equipment (type 11). And also the more standard hose, which is perfect for various environments. All models are highly reliable and excellent quality. All models are highly reliable and excellent quality.

General Specifications

Colour	Natural
Material	Nylon
Number Of Tubes	1
Special Features	Highly Flexible
Application	Air Brake, Fuel & Lube Applications, Industrial & Automotive Production Lines, Instrumentation & Secondary Air Systems

Mechanical Specifications

Hose Inside Diameter	7.5mm
Hose Outside Diameter	10mm
Length	30m

Operation Environment Specifications

Maximum Operating Pressure	17 bar
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+80°C