

# Specifications

## Eaton 3P550F

Eaton 3P Ellipse UPS FR, 550 VA, 330 W,  
Input: C14, Outputs: (3) French, (1) French  
surge only, Tower

### General specifications

<b>PRODUCT NAME</b>	Eaton 3P Ellipse UPS
<b>CATALOG NUMBER</b>	3P550F
<b>EAN</b>	3553340621246
<b>PRODUCT LENGTH/DEPTH</b>	235 mm
<b>PRODUCT HEIGHT</b>	263 mm
<b>PRODUCT WIDTH</b>	81 mm
<b>PRODUCT WEIGHT</b>	3 kg
<b>WARRANTY</b>	3 year on electronics, 2 year on battery
<b>COMPLIANCES</b>	CE Marked LVD Directive (CB) EMC Directive RoHS Directive WEEE Directive Packaging Directive Batteries Directive IEC 61643-11
<b>CERTIFICATIONS</b>	IEC/EN 62040-1 IEC/EN 62040-2 IEC/EN 62040-3 CE UKCA Cm
<b>MODEL CODE</b>	Eaton 3P Ellipse 550 FR



Powering Business Worldwide

## Additional information

<b>USB INTERFACE</b>	No
<b>CONSTRUCTION TYPE</b>	Free standing model
<b>PACKAGE CONTENTS</b>	<ul style="list-style-type: none"><li>• Input cable</li><li>• Quick start</li><li>• Safety instructions</li></ul>
<b>PHASE (OUTPUT)</b>	1
<b>AUTO SHUTDOWN FUNCTION</b>	No
<b>COLOR</b>	Black
<b>EFFICIENCY AT MAX. LOAD</b>	97
<b>RACK MOUNTING KIT</b>	No
<b>PHASE (INPUT)</b>	1
<b>SURGE PROTECTION</b>	Yes

## Communication

<b>INCLUDES NETWORK CARD</b>	No
<b>ETHERNET INTERFACE</b>	No
<b>USER INTERFACE</b>	LED display
<b>POTENTIAL FREE SWITCH CONTACT</b>	No
<b>EXPANSION SLOTS</b>	No
<b>TYPE OF INTERFACE</b>	None

## Electrical output

<b>RECEPTACLE</b>	(3) French, (1) French surge only
<b>VOLTAGE</b>	230V
<b>WATTAGE</b>	330W
<b>OUTPUT POWER FACTOR</b>	0.6
<b>OUTPUT VOLTAGE RANGE</b>	184-264 V (adjustable to 161-284 V)
<b>OUTPUT NOMINAL VOLTAGE</b>	230V default (220/230/240V)
<b>FEED TYPE</b>	1
<b>TOPOLOGY</b>	Offline
<b>VA RATING</b>	550 VA

## Battery

<b>BATTERY TYPE</b>	Sealed, lead-acid
<b>RUNTIME GRAPH</b>	<a href="#">View runtime graph</a>
<b>BATTERY QUANTITY</b>	1
<b>BATTERY MANAGEMENT</b>	Replaceable batteries, Automatic battery test, deep-discharge protection, cold-start capable
<b>BATTERY RATING</b>	12 V / 4.5 Ah
<b>EXTENDED BATTERY CAPABILITY</b>	No

## Electrical input

<b>INPUT CONNECTION</b>	C14
<b>INPUT NOMINAL VOLTAGE</b>	230V default (220/230/240V)
<b>NOMINAL FREQUENCY</b>	50-60 Hz
<b>INPUT CORD LENGTH</b>	1.5 m
<b>INPUT VOLTAGE RANGE</b>	184-264 V (adjustable to 161-284 V)
<b>INPUT FREQUENCY RANGE</b>	46-70 Hz

## Environmental

<b>ALTITUDE</b>	3000 m
<b>NOISE LEVEL</b>	<25 dB at 1 meter
<b>TEMPERATURE RANGE</b>	0° to 40°C (32° to 104°F)
<b>RELATIVE HUMIDITY</b>	0 - 95 % (non-condensing)

## Resources

BROCHURES	<a href="#">Eaton 3P Ellipse UPS brochure - EN</a>
DECLARATIONS OF CONFORMITY	<a href="#">Eaton 3P Ellipse UPS declaration of conformity - EN</a>
MANUALS AND USER GUIDES	<a href="#">Eaton 3P Ellipse UPS advanced user guide</a> <a href="#">Eaton 3P Ellipse UPS Quickstart guide</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

