



ENGLISH

Datasheet

Stock No. 161-7263

RS PRO Horizontal PDU 4 NF2P+T socket 3 m CEE7/7



DIN49441 16 A plug (CEE7/7)



## **SPECIFICATIONS:**

**Product Name:** Designated Power Distribution Unit for Cabinet

**Socket Type:** NF 2P+T socket (NFC61-314)

**Socket Quantity:** 4

**Power Input:** Left end single input

**Bracket Install:** Frontal installation

**Cable with plug:** DIN49441 16 A plug (CEE7/7)

**Control Function:** No controlling function

**Protection Function:** 2017 hot swaps module base

**Case:** Black

**Cable Specification:** 3 x 1.5 mm<sup>2</sup> x 3 M

**Product Size:** L x W x H = 468.5 x 44.4 x 44.4 mm

**Mounting Length:** 447.5 mm

**Case Length:** 415.5 mm

**Fittings:** 2 pcs  $\phi 6 \times 16$  mm cross bolt, 2 pcs M6 float nut, PDU manual, 1 pc 155 mm cover plate

### **Electrical Characteristics:**

**Rating voltage:** 250 V ac 50/60 Hz

**Rating Current:** 16 A

**Max. Power:** 4000 W

**Safety Authentication:** CE

**Operating Temperature:** 0 - 50°C, relative humidity 0 - 95%

### **Applications:**

PDU - Power Distribution Unit is widely used in network enclosure and server rack of data center in field of information technology, telecom, electric, power, finance and insurance, aviation, transportation, hospital, education, E-government etc.