

## Features

- Ø24mm cutout
- Nylon body
- Solder contacts
- Panel mounting

## RS PRO Panel Mount XLR Connector, 3 Way, Male

RS Stock No.: 0588692



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Buy this product from <https://uk.rs-online.com/>

Page 1 of 3

These professional, high quality XLR audio connectors are can be used in numerous applications including professional and consumer audio, broadcast and industrial uses.

They feature a tough nylon body and offer an economical alternative to high priced, metal XLRs.

## General Specifications

Gender	Male
Mounting Type	Panel Mounting
Body Orientation	Straight
No of Contacts	3
Type of Contact	Solder

## Mechanical Specifications

Body Material	Nylon
Contact Material	Brass
Contact Plating	Nickel Silver
Operating Temperature	-30°C to +80°C
Insertion Life	>1000 insertions
Insertion force	<10N

## Electrical Specifications

Current Rating	5A per pin (15A max)
Voltage Rating	250VAC max
Contact Resistance (new)	10mΩ (new), 15mΩ (after 1000 insertions)
Dielectric Withstand	1600VAC between all contacts
Insulation Resistance	10 <sup>9</sup> Ω at 500VDC
Capacitance between contacts	<5pF

## Approvals

Standards Met	RoHS
---------------	------

