

Product data sheet

Specifications



Repacked, socket-outlet, Mureva Styl, 2P + E with shutters, pin earth, 16A, 250V, surface, anthracite

MUR36030W



This repacked option saves 0.858 over the standard condition

Main

Range	Mureva Styl
Range of product	Mureva Styl
Product or component type	Socket-outlet
Device presentation	Complete product
Outlet poles configuration	2P + E
Outlet standard description	Pin earth
Outlet standard deviation	French
Colour tint	Anthracite (RAL 7016)

Complementary

Device mounting	Surface
Socket number	1
Rated current	16 A
[Ue] rated operational voltage	250 V AC
Condition of use	Indoor/outdoor
Material	Brass PP (polypropylene) PC (polycarbonate)
fixing mode	Screws
Cable entry	Easy valve access diameter: 6...12 mm
Height	76 mm
Width	76 mm
Depth	64 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Outlet standard	CEE 7/5
surface treatment	Untreated
Surface finish	Matt

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ue] rated operational voltage	250 V
Network frequency	50/60 Hz
Connections - terminals	Screw terminals

Environment

Quality labels	NF
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	7.600 cm
Package 1 Length	7.600 cm
Package 1 Weight	142.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.144 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.9 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

52b60409-d705-46c7-9ba3-cc3ef6e307da

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins