

Flexible chemical-resistant gloves, suitable for a wide range of applications

- **Advanced protection:** Suited to heavy-duty cleaning applications, these AlphaTec® gloves' nitrile compound and 0.425mm thickness ensure strength, chemical resistance and protection against snags, punctures and abrasion
- **Optimized comfort:** AlphaTec® 37-695 protective gloves also feature internal cotton flocking, which limits sweat buildup and enhances wearer comfort
- **Improved grip:** Thanks to their reversed lozenge finish, these durable work gloves boast excellent levels of grip in both dry and wet environments
- **Assured flexibility:** Their nitrile composition means they remain flexible and dexterous, for simpler everyday use



Industries

- Automotive
- Automotive Aftermarket
- Food Processing
- Metal fabrication
- Oil and gas
- Chemical

Applications

- Delivery of parts to production line
- Welding
- All food processing applications that have food contact
- Forging operations
- General pumping work
- Handling incoming goods
- Filling, blending and charging of raw materials
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Testing
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Painting or cleaning tools or robots

AlphaTec® Solvex®

37-695

Excellent chemical protection with a good level of grip, fit and comfort

Previously known as: Solvex® 37-695

Key Features

- **0.425mm nitrile compound:** Enhanced strength and chemical resistance
- **Cotton flocking:** Reduced perspiration buildup, for sustained comfort
- **Reversed lozenge finish:** For protective gloves offering better grip

Vulcanization Chemical Accelerators

- Mercaptobenzothiazole
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



0493

EN388: 2016



4101A

EN ISO 374-1:2016



AJKLPT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® Solvex® 37-695	Liner Material: N/A Coating Material: Nitrile	7, 8, 9, 10, 11	380 / 15	Green	• 12 pairs/polybag, 6 polybags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell