



Operational characteristics

Rated supply voltage AC	VAC	24
Rated supply voltage DC	VDC	24
Rated frequency	Hz	45...65
In-rush consumption	VA	0.58
Operating voltage	US	70...110
Average opening time	ms	50

Mechanical features

Tightening torque for terminals	min	Nm	0.8
	max	Nm	1
	min	Ibin	7
	max	Ibin	9


Conductor section

AWG/Kcmil	min	20	
	max	16	
Flexible w/o lug conductor section	min	mm ²	0.5
	max	mm ²	1.5
Flexible c/w lug conductor section	min	mm ²	0.5
	max	mm ²	1.5

Terminals

type	Screw
tool	PZ2

Weight	g	50
--------	---	----



Wiring diagrams

Certifications and compliance

Certificates

ETIM classification

EC000066 - Power contactor, AC switching