## 3M™ Cloth and Duct Tapes













Product number	1900	2903	2904	389	8979
Properties/suitable for	Value duct tape	General purpose	Heavy duty	Extra heavy duty	Clean removal
Key features (info box)					

Physical and Performance Characteristics, Key Features						
Product number	1900	2903	2904	389	8979	
Total thickness [mm]	0.17	0.15	0.19	0.26	0.29	
Adhesive type	Synthetic rubber resin	Synthetic rubber resin	Synthetic rubber resin	Crosslinked rubber resin	Rubber	
Colour	Silver, black	Silver, black	Silver, black	Silver, black, white, yellow, red, blue, green, olive	Slate blue	
Backing material	PE over coated cloth scrim	PE coated cloth scrim	PE coated cloth scrim	PE coated cloth scrim	PE coated cloth scrim	
Peel strength [Newton/25 mm]	15	20	27.5	22.5	15.5	
Tensile strength [Newton/25 mm]	70	100	110	200	160	
Elongation at break	20%	30%	30%	6%	17%	
Temperature resistance (min, h)	60 °C	60 °C	60 °C	70 °C	93 °C	
Indoor and outdoor use						
Clean removal						

Suggested Applications					
Product number	1900	2903	2904	389	8979
Lighter duty applications such as bundling, sealing, holding, labelling and identifying in non-critical applications	•				
Temporary repairing, bundling, reinforcing	•	•			
Fixing, closing, packaging		•			
General maintenance, repair and protection		•	•		
Pipe wrapping and duct seaming		•	•		
Marking and labeling		•	•		
Bundling, sealing, semi permanent repair operations			•		
Building and construction market applications			•		
Colour coding, marking and labeling				•	
Joining and sealing of sheetings, wallboards, metal and plastic ducting				•	•
Splicing of insulation, pipes and panels (hinge effect)				•	•
Cauling and protection with film splicing for treatment or decontamination				•	•
Wrapping of containers and pipes				•	•
Container sealing and tarp repair				•	•
Outdoor duct tape applications and temporary weather sealing					•
Product number	1900	2903	2904	389	8979

## Product Use